

Specification AD/CV1200/Issue 2. Dated : 6.12.47. To be read in conjunction with K1001.	<u>SECURITY</u>	
	<u>Specn.</u> Restricted	<u>Valve.</u> Unclassified

→ indicates a change.

<u>TYPE OF VALVE:-</u> Current Stabiliser		<u>MARKING</u>	
<u>ENVELOPE:-</u> Glass, clear		See K1001/4.	
<u>PROTOTYPE:-</u> Barretter 202		<u>BASE</u> BL	
		See K1001/AIV/D5.1	
<u>RATING</u>		<u>Pin</u>	<u>Electrode</u>
Max. Filament Current (A)	0.2	1	No Connection
Voltage range (V)	120 to 200	2	No Connection
		3	Filament
		4	Filament
	<u>Note</u>	<u>DIMENSIONS</u>	
		See K1001/A1/D1.	
		<u>Dimension</u>	<u>Min.</u> <u>Max.</u>
		A mm	- 154
		B mm	- 64
		<u>PACKAGING</u>	
		See K1005.	

TESTS

To be performed in addition to those applicable in K1001

	Test Conditions	Test	Limits		No. Tested
			Min.	Max.	
a	Vf(V) = 120	If after 5 minutes (A)	0.185	-	100%
b	Vf(V) = 200	If after 5 minutes (A)	-	0.215	100%